

According to the Regulation (EU) 2016/425 of the European Parliament and of the Council of 9 March 2016 on personal protective equipment and repealing Council Directive 89/686/EEC

**A.N.C.I. Servizi s.r.l. a socio unico – CIMAC Laboratories**  
**Community Identification N° 0465**

Grants:  
Manufacturer  
**COFRA S.R.L.**  
**VIA DELL'EURO 53-57-59**  
**76121 BARLETTA**

**EU TYPE-EXAMINATION CERTIFICATE MODULE B**  
**N° F-100-03910-20**

for the following model of Personal Protective Equipment:

**Design/Item:** Ankle boot art. PUSHPRESS BROWN - 1353  
**Category of PPE:** II  
**Additional requirements:** S3 SRC

safety footwear for professional use according to harmonized standard (\*)  
EN ISO 20345:2011

**Picture of the basic model**



**First issue date: 17/11/2020**  
**Revision date:**  
**Expiry date: 17/11/2025**

Technical Manager  
Giuseppe Bellotti

EU Type-Examination Certificate n. F-100-03910-20 of 17/11/2020 - Page: 1 of 3 2020\2582-7

|  |  |   |                     |       |            |
|--|--|---|---------------------|-------|------------|
| <b>Manufacturer's identification mark:</b> | COFRA  |   |                     |       |            |
| <b>Classification:</b>                     | I - Footwear made from leather and other materials, excluding all-rubber or all-polymeric footwear |   |                     |       |            |
| <b>Size range:</b>                         | from 36 to 48 (french point)   |   |                     |       |            |
| <b>Identification of last:</b>             | A1035/5  |   |                     |       |            |
| <b>Manufacturing process:</b>              | Injection  |   |                     |       |            |
| <b>The footwear has a:</b>                 | non-metallic toecap  | cod                                     | AAC03(XKY189)       |       |            |
|  | non-metallic penetration-resistant insert  | cod                                     | OSD31.xxx.F04       |       |            |
|  | removable insock   | cod                                     | SP034               |       |            |
| <b>Additional requirements:</b>            | heel area closed;  |   |                     |       |            |
|  | A  | antistatic properties;                  |                     |       |            |
|  | E  | energy absorption of seat region;       |                     |       |            |
|  | WRU  | water resistant upper                   |                     |       |            |
|  | P  | penetration resistance of sole complex; |                     |       |            |
|  | FO   | fuel oil resistant outsole;             |                     |       |            |
|  |  | cleated outsole.                        |                     |       |            |
| <b>Test Reports:</b>                       | The results of tests and examinations are contained in the following test reports:                 |   |                     |       |            |
|  | Whole footwear   | CIMAC                                   | RP 2020\2580-7-RP-1 | dated | 15/10/2020 |
|  | Bottom of the footwear   | CIMAC                                   | RP 2020\2420-2-RP-1 | dated | 06/10/2020 |
|  | Upper  | CIMAC                                   | RP 2020\2420-3-RP-1 | dated | 06/10/2020 |
|  |  | CIMAC                                   | RP 2019\1493-2-RP-4 | dated | 06/09/2019 |
|  | Toecap   | CIMAC                                   | RP 2019\3967-1-RP-1 | dated | 15/01/2020 |
|  | Vamp lining  | CIMAC                                   | RP 2017\2479-1-RP-2 | dated | 24/11/2017 |
|  |  | CIMAC                                   | RP 2017\2479-1-RP-4 | dated | 24/11/2017 |
|  | Quarter lining   | CIMAC                                   | RP 2019\0514-1-RP-2 | dated | 11/04/2019 |
|  |  | CIMAC                                   | RP 2019\0514-1-RP-4 | dated | 11/04/2019 |
|  | Seat region lining   | CIMAC                                   | RP 2018\0972-1-RP-2 | dated | 15/05/2018 |
|  |  | CIMAC                                   | RP 2018\0972-1-RP-4 | dated | 15/05/2018 |
|  | Collar   | CIMAC                                   | RP 2016\1948-1-RP-2 | dated | 03/11/2016 |
|  |  | CIMAC                                   | RP 2016\1948-1-RP-2 | dated | 03/11/2016 |
|  | Tongue   | CIMAC                                   | RP 2019\3788-4-RP-1 | dated | 17/01/2020 |
|  | Removable insock   | CIMAC                                   | RP 2020\2420-4-RP-1 | dated | 06/10/2020 |
|  | Insock   | CIMAC                                   | RP 2020\2420-5-RP-1 | dated | 06/10/2020 |
|  | Penetration-resistant insert   | CIMAC                                   | RP 2020\2420-6-RP-1 | dated | 06/10/2020 |
|  | Outsole  | CIMAC                                   | RP 2020\2420-7-RP-1 | dated | 06/10/2020 |

## Marking



CE Marking

Name and postal address of the Manufacturer  
manufacturer's type designation  
the number and year of the reference European standard  
Category and additional requirements of the PPE  
Month and year of fabrication  
Size  
Batch number  
Reference to informative note



(\*) Subsystems and safety components which are in conformity with harmonised standards or parts thereof the references of which have been published in the Official Journal of the European Union shall be presumed to be in conformity with the essential requirements set out in Annex II Regulation (EU) 2016/425.

**Validity conditions:** This certificate is valid for 5 years from the date of issue. On expiration the manufacturer shall ask for its renewal. The rules applied are those in force on the date of issue shown on this certificate; The validity of the certificate is no longer guaranteed if substitutive standards are issued before the expiration date. All changes made to the model and to the materials described in this EU type-examination certificate shall be reported to and approved by CIMAC. This EC Type-Examination Certificate may be integrally duplicated; the copy must be faithful, legible (if pint size) and must contain the bold caption "TRUE COPY". This certificate must be kept by the manufacturer to be shown, on request, to the inspection or notifying authorities.